

REO-PURE™ LP3 225-1750 SERIES ORDERING GUIDE



ITEM NUMBER: #1 #2 #3 #4 #5 #6 #7 #8 #9
 - - - - - - -

#1 - MODEL (SELECTION REQUIRED)

- 1 - Standard
- 2 - Optimum

#2 - GPD (SELECTION REQUIRED)

0225 0350 0500
0750 1000 1750

#3 - MATERIAL (SELECTION REQUIRED)

- 1 - Standard*
- 8 - Stainless Steel
- 9 - Lead Free

#4 - MEMBRANE (SELECTION REQUIRED)

- 1 - Standard*
- 2 - Filmtec Standard[†]
- 6 - Filmtec NF270[†]
- 8 - Filmtec LCLE[†]

#5 - FILTER (SELECTION REQUIRED)

- 1 - Standard*

#6 - SHUTOFF TYPE (SELECTION REQUIRED)

- 1 - Product Pressure Switch*
- 2 - ATMO, No Float
- 3 - ATMO, Float Package

#7 - MONITOR

- 1 - TDS Push-to-Test, QC-1, Single Probe
- 2 - TDS Digital, SM-1, Single Probe
- 4 - TDS Digital, DM-2, Dual Probe

#8 - PACKAGING

- 3 - Export, Full Wooden Crate

#9 - CUSTOM OPTIONS

- 1 - Blending Valve, TDS, Includes Monitor



LP3-1750 Optimum
(Shown w/ Flexwave SSRO40 & Grundfos SCALA2)

* Designates a standard feature included with the base model

[†] Not available for all models



TEL: 262.634.2386 | TOLL FREE: 800.357.8538

FAX: 262.634.6259 | TOLL FREE: 888.700.6144

For items not listed, please call for additional information.

EMAIL: sales@greatlakesintl.com

WEB: greatlakesintl.com

03062026